

# THERMOLAST® H - HC/AD1/AP Series For Asia Pacific Healthcare & Medical Device Applications





## Our Know-how - Your Advantage

THERMOLAST® H is a new range of TPE designed for the healthcare and medical device applications in Asia Pacific. The HC/AD1/AP series provides high-quality material solutions which comply with Cytotoxicity ISO 10993-5 and GB/T 16886.5. The series is characterized by its superior adhesion to polar thermoplastics such as PC, ABS, PETG, etc.

- Hardness range from 30 to 80 ShA
- Adhesion to PC, ABS, PC/ABS, PETG, PCTG
- Optimized mechanical properties
- Soft touch surface
- Pre-coloration available in-house
- Free from animal ingredients
- Free of PVC, latex, and heavy metals
- REACH SVHC
- RoHS Directive
- All raw materials are (EU) No. 10/2011, and US FDA CFR 21 approved
- Bio-compatibility testing according to ISO 10993-5 and GB/T 16886.5
- Sterilizable

# **Heng Hooi Chi**Product Specialist

"THERMOLAST® H is your material solution for healthcare and medical device application needs with superior adhesion to engineering thermoplastics such PC, ABS, PETG, etc. Our high-quality material solutions meet Asia Pacific medical standards and custom-engineered support at all project stages upon request."

#### **Aditya Purandare**

Project Manager Market Launch THERMOLAST® H Asia Pacific

"Manufacturing THRMOLAST® H, the exclusively designed TPE for the Asia Pacific medical device market requirements will benefit our customers with a high-quality product, quick lead times, application and technical support as well as product customization."

## **Typical Applications**

- Seals
- Push buttons
- Handles

- Valves
- Grips
- Flexible connectors







#### **Technical Data**

	Unit	TH4PGM- NTRL	TH6PGM- NTRL	TH8PGM- NTRL
Density	g/cm³	0.940	0.960	1.030
Hardness	Sh A	40	60	80
Tensile Strength¹	MPa	5.0	7.0	11.0
Elong. at Break¹	%	600	650	700
Tear Resistance	N/mm	9.5	13.0	23.0
Adhesion to PC <sup>2</sup>	N/mm	3.7 D	5.1 D	9.7 B/D
Adhesion to ABS²	N/mm	2.4 A	3.2 A	3.7 A
Adhesion to PC/ABS <sup>2</sup>	N/mm	2.7 A	5.2 D	10.0 C/D
Adhesion to PETG <sup>2</sup>	N/mm	2.6 A	4.9 D	9.9 C/D

Deviating from ISO 37 standard test piece S2 is tested with a traverse speed of 200mm/min.

#### **TALK TO OUR EXPERTS!**

KRAIBURG TPE TECHNOLOGY (M) SDN. BHD. - ASIA PACIFIC

info-asia@kraiburg-tpe.com

KRAIBURG TPE GMBH & CO. KG - EUROPE, MIDDLE EAST, AFRICA

info@kraiburg-tpe.com

**KRAIBURG TPE CORPORATION - AMERICAS** 

info-america@kraiburg-tpe.com

<sup>&</sup>lt;sup>2</sup> The adhesion quality depends on mold design, product geometry and process parameters.